



FULL FACE MASK TR 82 IN SILICONE

Cod. 112170000

Full Face Mask, Negative Pressure, with threaded connector to EN 148-1 made of:

- Moulded face blank
- Visor, panoramic and wide visibility
- Group that holds in one single body the connection for the filter or respirator, the exhale membranes, the inhalation membrane and the speech device.
- Inner nose cup
- Head harness, five arms
- Neck strap

The mask can be used with negative pressure devices provided with the same threaded connector to EN 148-1, such as filters, air lines AC190, etc



TECHNICAL DATA

Breathing Resistance:

Test flow	Inhalation mbar		Exhalation mbar	
	Standard	Measured	Standard	Measured
25 cycles/min x 2 l/cycle	≤ 2.5	1.3	≤ 3.0	1.8
30 l/min	≤ 0.5	0.1		
95 l/min	≤ 1.5	0.7		

Inward Leakage

Test gas	Max admitted inv. Leakage %	Measured Penetration % (10 subjects average)
SF6	0.05	< 0.03

Limitations for use

The mask cannot be used with positive pressure SCBAs nor with devices not provided with the same connector to EN 148-1

CLASSIFICATION

Full Face Mask, Class 3 to **EN 136:1998** and Directive **89/686/EEC (PPE)**.





YOUR SAFETY MAKER



FULL FACE MASK TR 82 IN SILICONE

Cod. 112170000

MARKING



MATERIALS

Face Blank:	Silicone
Visor:	Polycarbonate scratch and solvent resistant
Head harness:	Silicone
Nose Cup:	TPE
Neck strap:	PVC

STORAGE

Store at temperatures between -20 and +50 °C and RH <80%

WEIGHT

580 g (1,25 lb) approximately

DIMENSIONS/PACKAGING

The mask is delivered in a PE bag into a single carton box, dimensions 230x175x125 mm (9.05 x 6.89 x 4.92 in).
Masks come in a multiple 6 pieces carton, dimensions 470x390x200 mm (18.50 x 15.35 x 7.87 in)

For more information please check the notes along with the products or the ones published on the website: www.spasciani.com

NOTE: SPASCIANI SpA does not take any responsibility for any possible and unintentional mistake and reserve the faculty of modify materials and technical characteristics of its products at any time and without any notice.

